

We, Rollease Acmeda Inc, hereby stated that the flow tube motor will be manufactured with different models as shown in the following table. In addition to the software and the following table differences, the following models may also use different color shell, and these differences will not affect the RF parameters:

Model name	The Same Part	The different Part
MT01-1335-069002	Have the same motor, RF board, control board,	Shell diameter 35mm, suitable for 35mm size of plastic parts, Use 54Wh capacity battery
MT01-1345-069003		The diameter of the shell is 45mm, and the inner tube and plastic parts of 45mm are adapted, Using a 56.16Wh capacity battery, the difference between the two models is the difference in deceleration components
MT01-1345-069004		

Yours sincerely,



Print name: Jonny.Matuichuk

Title: Product Manager

Date:26/03/2025