

2019/05/08

To whom it may concern :

This document explain the difference between the model SE100-V (Model tested) and the rest of the family (SE100-V-2, SA100-HT, SE100-T, SG100-V2).

SE100-V-2 : Everything is the same, but in this model we have two vacuum sensors instead of one

SA100-HT : Everything is the same, but in this model we have ultrasonic sensor instead of vacuum sensor.

SE100-T : Everything is the same, but in this model works with accessories (Pump Starter)

SG100-V2 : Everything is the same, but in this model we have ethernet port to be able to communication on local area network (LAN).

ANTENNAS:

Cloverleaf antenna 21009: Gain 2.5 dBi peak gain

Dipole antenna 21008: Gain 5 dBi peak gain



Martin Berube
Product Manager Monitoring System