



January 17, 2022

RE: Differences Between Module B01-007A and B01-007B

To Whom It May Concern,

The RF performance/RF design and antenna type between the two models are identical. The difference between the two models is: model B01-007A is a larger PCB and uses a capacitive touch sensor to determine movements. Model B01-007B is a smaller PCB that uses a hall effect sensor to determine if the trap is open or closed.

Signed:

Joe Triventi
Joe Triventi (Jan 17, 2022 15:52 EST)

Printed Name: Joe Triventi

Title: Engineering Manager

On behalf of: Smartwave Technologies

B01-007A-B_Differences_v2

Final Audit Report

2022-01-17

Created:	2022-01-17
By:	Gavin Singh (gavin@smartwave.ca)
Status:	Signed
Transaction ID:	CBJCHBCAABAAHkbPP3ST1eKoWSvDSKdIXo6rYphb2LCw

"B01-007A-B_Differences_v2" History

-  Document created by Gavin Singh (gavin@smartwave.ca)
2022-01-17 - 8:45:13 PM GMT- IP address: 192.0.251.233
-  Document emailed to Joe Triventi (joet@smartwave.ca) for signature
2022-01-17 - 8:45:28 PM GMT
-  Email viewed by Joe Triventi (joet@smartwave.ca)
2022-01-17 - 8:51:36 PM GMT- IP address: 99.229.122.61
-  Document e-signed by Joe Triventi (joet@smartwave.ca)
Signature Date: 2022-01-17 - 8:52:09 PM GMT - Time Source: server- IP address: 99.229.122.61
-  Agreement completed.
2022-01-17 - 8:52:09 PM GMT