

單色印刷 - 90%K 深灰色
完成尺寸12x12 CM

封底

封面

START

APP downloading, wearing and software operation



singularinfo.com/beatinfoX

FEDERAL COMMUNICATIONS COMMISSION

INTERFERENCE STATEMENT

The equipment has been tested and found to comply with the limits for a Class B digital device, pursuant to Part 15 of the FCC Rules. These limits are designed to provide reasonable protection against harmful interference in a residential installation. This equipment generates, uses, and can radiate radio frequency energy and, if not installed and used in accordance with the instructions, may cause harmful interference to radio communications. However, there is no guarantee that interference will not occur in a particular installation. If this equipment does cause harmful interference to radio or television reception, which can be determined by turning the equipment off and on, the user is encouraged to try to correct the interference by one or more of the following measures:

- Reorient or relocate the receiving antenna.
 - Increase the separation between the equipment and receiver.
 - Connect the equipment into an outlet on a circuit different from that to which the receiver is connected.
 - Consult the dealer or an experienced radio/TV technician for help.
- This device complies with Part 15 of the FCC Rules. Operation is subject to the following two conditions:
- (1) This device may not cause harmful interference, and
 - (2) this device must accept any interference received, including interference that may cause undesired operation.

CAUTION:

To avoid voiding FCC compliance:

Any changes or modifications not expressly approved by the grantee of this device could void the user's authority to operate the equipment. FCC/CE/Redundant System Statement This equipment complies with FCC/CE radio frequency limits and limits for an uncontrolled environment. This transmitter must not be controlled or operating in conjunction with any other transmitter or equipment.

低功率射頻電機標籤

第十二條 經型式認證合格之低功率射頻電機，非經許可，公司、廠牌或使用者均不得擅自變更標籤，並不得在標籤上加註其他文字或圖示。

第十四條 低功率射頻電機之使用不得造成無線電波干擾或干擾合法通信；除應有干擾防護外，並應採取必要之防止干擾措施。除應符合電磁相容性標準外，並應符合國家標準 CNS 15715 之規定。

OTHERS

If design award 1 year warranty (non-made exclusive)

Heart Rate Transmitter HR-100 User Guide



NOTE

Thank you for using the Heart Rate Transmitter HR-100! This article will take you through the basic use of the heart rate Heart Rate Transmitter HR-100. Use Heart Rate Transmitter HR-100 needs to be equipped with accessories (such as patch, elastic chest strap, smart clothes, etc.) to measure physiological information; please contact dealer for additional accessories.

The Heart Rate Transmitter HR-100 proprietary app "Beatinfo X" is compatible with a wide range of smartphones. If it is not compatible, it is recommended to update the smartphone's operating system.

The signal transmitted by the Heart Rate Transmitter HR-100 does not pass through the human body, so the smartphone should be placed in front of you and the smartphone should not be placed in a bag or cabinet.

Clean Heart Rate Transmitter HR-100 with a wet towel, and then store after it is completely dry.

For the first time, please use Charging dock to charge. If you have any questions about how to use it, you can visit the Beatinfo product website at www.beatinfo.biz for more detailed instructions and instructions.

Charging and connection

It takes about 2 hours to full charge. The flashing red light indicates that charging is in progress, and the green light indicates that charging has been completed.

Turn on

Press the button on Heart Rate Transmitter HR-100. The indicator light flashes red once and continues to flash blue to indicate that the power is on.

Turn off

Press the button on Heart Rate Transmitter HR-100. It indicates that the power has been turned off when Heart Rate Transmitter HR-100 vibrates twice.

Bluetooth connection

The flashing blue light indicates under searching. Flashing green light and vibration indicates that Heart Rate Transmitter HR-100 is connected to the phone.

SPECIFICATION

尺寸 Dimensions 38.5mm x 38.5mm x 9.5mm

材質 Material Housing: PC/ABS, Electrode: stainless

重量 Net Weight 25g (0.9oz)

生理資訊 Physiological Sensor Heart rate, RR interval, heart signal

心率 Heart Rate 50-160 bpm (1.5 bpm)

心跳間隔 RR Interval 350-1000 (1.0/100 ms)

心跳間隔 Sampling Rate (Hz) 250 Hz

使用環境溫度 Operating Temperature 15°C-32°C (59°F-122°F)

防水等級及標籤 Alarm Feedback and Indicator RGB LED & Motor Vibration

無線傳輸介面 Communication 2.4 GHz

無線傳輸距離 Transmission Range Up to 3 meters (10 feet)

數據傳輸速率 Data Rate Coriolis 9.6K

電池類型 Power Supply 1.5m polymer

充電時間 Charging Time to Full 2-3 hours

充電溫度 Charging Temperature 15°C-32°C (59°F-122°F)

心跳間隔 Sampling Rate (Hz) 250 Hz

心跳間隔 RR Interval 350-1000 (1.0/100 ms)

心跳間隔 Sampling Rate (Hz) 250 Hz