

Google

 g.co/pixel/help


 g.co/switchtopixel

 g.co/pixel/protection

GV53-62220-02-02

Set up your Pixel phone

You can move what's on your current phone to your Pixel phone, or set up your Pixel phone as a new device by viiting g.co/pixel/help



1. Pixel phone
2. SIM tool
3. 1 m USB-C to USB-C cable (USB 2.0)

Regulatory Information

Regulatory information, certification, and compliance marks specific to your phone can be found on your device under **Settings > About phone > Regulatory labels** and/or on the back of your device.

EMC COMPLIANCE STATEMENT

Important: This device and other in-box accessories have demonstrated Electromagnetic Compatibility (EMC) compliance under conditions that included the use of compliant peripheral devices and shielded cables between system components. It is important that you use compliant peripheral devices and shielded cables between system components to reduce the possibility of causing interference to radios, televisions and other electronic devices.

FCC REGULATORY COMPLIANCE

Note: This equipment has been tested and found to comply with the limits for a Class B digital device, pursuant to part 15 of the FCC Rules. These limits are designed to provide reasonable protection against harmful interference in a residential installation. This equipment generates, uses, and can radiate radio frequency energy and, if not installed and used in accordance with the instructions, may cause harmful interference to radio communications. However, there is no guarantee that interference will not occur in a particular installation. If this equipment does cause harmful interference to radio or television reception, which

can be determined by turning the equipment off and on, the user is encouraged to try to correct the interference by one or more of the following measures:

- Reorient or relocate the receiving antenna.
- Increase the separation between the equipment and receiver.
- Connect the equipment into an outlet on a circuit different from that to which the receiver is connected.
- Consult the dealer or an experienced radio/TV technician for help.

Changes or modifications not expressly approved by Google could void your authority to operate the equipment.

This device complies with Part 15 of the FCC Rules. Operation is subject to the following 2 conditions:

1. These devices may not cause harmful interference.
2. These devices must accept any interference received, including interference that may cause undesired operation.

The operation of this device is prohibited on oil platforms and aircraft, except that operation of this device in 5.925-6.425 GHz is permitted in large aircraft while flying above 10,000 feet.

Installation on outdoor fixed infrastructure is prohibited.

Operation of transmitters in the 5.925-7.125 GHz band is prohibited for control of or communications with unmanned aircraft systems, including drones.

Model number: GTF7P
US Responsible Party
Google LLC
1600 Amphitheatre Parkway
Mountain View, CA 94043
Contact: g.co/pixel/contact

Radio Frequency Exposure

This device has been evaluated and meets the applicable regulatory requirements for exposure to radio waves and is designed and manufactured not to exceed the applicable emission limits for exposure to radio frequency (RF) energy.

Your phone complies with RF specifications when

used near your ear or at a distance of 0.4 in (1.0 cm) from your body. To reduce exposure to RF energy, use a hands-free option, such as the built-in speaker phone, the supplied headphones, or other similar accessories. Ensure that the device accessories, such as a device case and device holster, are not composed of metal components. Keep the device away from your body to meet the distance requirement.

You can find the Specific Absorption Rate (SAR) values applicable to each of those jurisdictions on your device: **Settings > About phone > Regulatory labels**.

To reduce exposure to RF energy, use a hands-free option, such as the built-in speakerphone, the supplied headphones, or other similar accessories. Ensure that the device accessories, such as a device case and device holster, are not composed of metal components. Keep the device away from your body to meet the distance requirement.

HEARING AID COMPATIBILITY (HAC)

This phone is hearing aid compatible as determined by ANSI C63.19-2019, amended under the conditions of FCC limited waiver DA 23-914. The ANSI C63.19-2019 standard does not use the rating system that older versions of the standard used, i.e., M rating, which is a measure of immunity to radio frequency interference for acoustic coupling hearing aids, and T rating, which is a measure of performance when used with an inductive coupling (telecoil) hearing aid. Specifically, the 2019 ANSI Standard requires that handsets meet volume control specifications in order to be considered hearing aid-compatible under that standard. Under the waiver, certain Volume Control test requirements are relaxed or waived and certain test configurations were partially or not tested. For instance, only Commercial Mobile Radio Services (CMRS) narrowband and CMRS wideband voice codecs are required to comply with the volume control requirements of the Volume Control Standard. All other codecs, such as full-band and super-wideband codecs or over-the-top (OTT) codecs, are not required to comply with the Volume Control Standard. In order to pass the volume control requirement, a handset must meet a two-part test. The first part of the requirement tests for conversational gain with a hearing aid, and the second part of the requirement tests for conversational gain without a hearing aid. To pass both parts of the requirement, a handset must have at least 6 dB of conversational gain with or without a hearing aid.

This phone has been evaluated and meets the volume control requirements per technical specification ANSI C63.19-2019 and under FCC limited waiver DA 23-914. The actual conversational gain for fully tested Enhanced Voice Services (EVS) narrowband and EVS wideband codecs and air interface combinations is 16.9 dB with hearing aids and 19.1 dB without hearing aids. The lowest conversational gain for partially tested Enhanced Full Rate (EFR), Adaptive Multi-Rate (AMR) narrowband, and AMR wideband codecs and air interface combinations is 17.2 dB with hearing aids and 19.1 dB without hearing aids.

This phone has been tested and certified for use with hearing aids for some of the wireless technologies that they use. However, there may be some newer wireless technologies used in this phone that have not been tested yet for use with hearing aids. It is important to try the different features of your phone thoroughly and in different locations, using your hearing aid or cochlear implant, to determine if you hear any interfering noise. Consult your service provider or Google for information on hearing aid compatibility. If you have questions about return or exchange policies, consult your service provider or phone retailer.

The table below shows the wireless technologies (including frequencies/bands by air interface and codec) that were tested or not tested according to FCC rules and limited waiver DA 23-914.

Air Interface	Bands	Codec	RFE	T-coil	Volume Control
LTE/ NR/ WIFI	LTE: 2/4/5/7/12/13/14/17/25/26/30/38/41/48/66/71 NR: n2/5/7/12/14/25/26/30/38/41/48/66/70/71/77/78 WIFI: 2.4 GHz, U-NII 1/2A/2C/3/4/5*	AMR-NB, AMR-WB, EVS-NB, EVS-WB	Yes	Yes	Yes
		EVS-SWB, OPUS	Yes	Yes	No
NR/ WIFI	WIFI: U-NII 5*/6/7/8	AMR-NB, AMR-WB, EVS-NB, EVS-WB, EVS-SWB, OPUS	No	No	No

UMTS/ GSM	UMTS: V, IV, II GSM: 850/1900	EFR (GSM only), AMR-NB, AMR-WB	Yes	Yes	Yes
	UMTS: V, IV, II GSM: 850/1900	OPUS	Yes	Yes	No

** U-NII 5 is tested for Hearing Aid Compatibility for channels which are entirely below 6 GHz. Channels partially or entirely above 6 GHz are not subject to testing.*