

## TO WHOM SO EVER IT MAY CONCERN

Gothenburg, 18<sup>th</sup> May 2010.

### MODEL DIFFERENCE LETTER, FCC ID: BXZDH5BL

This letter is to explain the differences between the different variants of Ascom DH5 handset with Bluetooth capability with the following model numbers:

**DH5-AABAAA (Model Messenger)**

**DH5-AABCAA (Model Protector with No Movement/Man Down sensors)**

**DH5-AABEAA (Model Protector with No Movement/Man Down sensors and Pull Cord)**

All DH5-xABxAA handsets will use the same PCB, FPC's and other electrical components i.e. speakers (loudspeaker and receiver), microphone, battery, vibrator and display. All plastic parts are the same between the versions.


For Brand:

- The branding plate is different (plastic marking).

For Features:

1. The version without Alarm will not have the electronic parts for the pull cord switch and the NM/MD mounted on the PCB. And the alarm button on top of the handset are removed in the plastics, the electronic switch are still mounted.
2. The versions without NM/MD will not have the components for NM/MD mounted on the PCB.
3. The version without Pull-Cord will have a lid over the mechanical connection of the "pull cord".

Very truly yours,



Lena Kindmark

Certification Engineer