



January 13, 2003

**Mr. Kent Stewart
EMC Testing Laboratories, Inc.
2210 Justin Trail
Alpharetta, GA 30004**

Ref: HQ Inc. Product No. HT130002

Dear Kent:

The external power source which is used to power the base station, is a regulated DC switching supply which can work on input AC power sources as defined in the external power source specification in our user's manual.

We will be using a DB 9 shielded cable for the serial cable connection between the computer and base station and we will use a special 6 pin shielded cable that we manufacture for the connection between the CorTemp and the RF remote unit as specified in our user's manual.

We will modify our user's manual to include a statement to use only the provided components (shielded RS-232 cable & power supply) that are supplied with the system.

**Sincerely,
HQ, Inc.**

**William S. Hicks
President**

/sys

941-721-7588 • FAX 941-729-5480 • Email: hti2000@gte.net • Website: htitech.com