

DECLARATION OF SIMILARITY

Date 01/04/2015

RE: Declaration of Similarity

To Whom It May Concern:

Please be advised that the model below is identical to the 20-0183-1

20-0184-1

"All models are electronically identical, all RF measurements and test results are exactly the same."

The difference between the models is the beam width of the sensor. 20-0183-1 is a wide beam sensor with a vision angle of 110°. 20-0184-1 is a narrow beam sensor with a vision angle of 11°

Transmission power is maintained at 100mW EIRP for both sensors.

Thank you for your attention to this matter.

Yours faithfully

Guidance Marine Ltd



Thomas James Coggins