


Notes:

- 1) Label material to be 3M 7872 Platinum Polyester (UL approved).
- 2) 1 mil clear matte polyester overlaminant required.
- 3) All print color to be black.
- 4) Label to be RoHS compliant per EU directive 2002/95/EC.
Statement of compliance to be available upon request.

		DIMENSIONS ARE IN INCHES		GENERAL DYNAMICS C4 Systems FORTRESS TECHNOLOGIES® ES520V1C Compliance Label	SIZE A DWG. NO. 410-00048-01 REV. 2 SCALE:1:1 SHEET 1 OF 1		
		TOLERANCES: FRACTIONAL \pm					
		ANGULAR: MACH \pm BEND \pm					
		TWO PLACE DECIMAL $\pm .01$					
		THREE PLACE DECIMAL $\pm .005$					
PROPRIETARY AND CONFIDENTIAL		2 Update for FCC approval.					
THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF FORTRESS TECHNOLOGIES. ANY REPRODUCTION IN PART OR AS A WHOLE WITHOUT THE WRITTEN PERMISSION OF FORTRESS TECHNOLOGIES IS PROHIBITED.		1 Initial release.					
REV		CHANGE DESC.					
REVISION HISTORY		FINISH					
REVISION HISTORY		DO NOT SCALE DRAWING					



Notes:

- 1) Label material to be 3M 7872 Platinum Polyester (UL approved).
- 2) 1 mil clear matte polyester overlaminant required.
- 3) All print color to be black.
- 4) Label to be RoHS compliant per EU directive 2002/95/EC.
Statement of compliance to be available upon request.

		DIMENSIONS ARE IN INCHES			NAME	DATE
		TOLERANCES:		DRAWN	JCB	08MAR12
		FRACTIONAL \pm		CHECKED		
		ANGULAR: MACH \pm BEND \pm		ENG APPR.		
		TWO PLACE DECIMAL $\pm .01$		MFG APPR.		
		THREE PLACE DECIMAL $\pm .005$		Q.A.		
				COMMENTS:		
PROPRIETARY AND CONFIDENTIAL		2 Update for FCC approval.				
THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF FORTRESS TECHNOLOGIES. ANY REPRODUCTION IN PART OR AS A WHOLE WITHOUT THE WRITTEN PERMISSION OF FORTRESS TECHNOLOGIES IS PROHIBITED.		1 Initial release.				
REV	CHANGE DESC.	MATERIAL				
		FINISH				
REVISION HISTORY		DO NOT SCALE DRAWING				

GENERAL DYNAMICS
C4 Systems

FORTRESS TECHNOLOGIES®

ES520V2
Compliance
Label

SIZE **A** DWG. NO. **410-00051-01** REV. **2**

SCALE:1:1 SHEET 1 OF 1

ES520 Compliance label location on bottom side of unit:

